

manifold rail

VABM-L1-14S-G14-14

Part number: 566628

FESTO



Data sheet

| Feature | Value |
|---|---------------------------------------|
| Grid dimension | 16 mm |
| Max. number of valve positions | 16 |
| Operating pressure MPa | -0.09 ... 1 MPa |
| Operating pressure | -0.9 ... 10 bar |
| Authorisation | RCM Mark c UL us - Recognized (OL) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Max. tightening torque, H-rail mounting | 1.5 Nm |
| Max. tightening torque, valve mounting | 0.65 Nm |
| Max. tightening torque, wall mounting | 3 Nm |
| Product weight | 610 g |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 3 | G1/4 |
| Pneumatic connection, port 5 | G1/4 |
| Materials note | Conforms to RoHS |
| Material manifold | Wrought Aluminium alloy |