


# mini slide

## DGSL-10-80-EA

Part number: 570177

FESTO



## Data sheet

| Feature  | Value   |
|--|---|
| Stroke   | 80 mm   |
| Adjustable endposition range/front length                | 37 mm   |
| Adjustable endposition range/rear length                 | 5.5 mm  |
| Piston diameter  | 12 mm   |
| Operating mode of drive unit                             | Yoke  |
| Cushioning   | Short elastic cushioning rings/pads at both ends                            |
| Assembly position  | Any   |
| Guide  | Ball bearing cage guide   |
| Design structure   | Yoke<br>Piston<br>Piston rod<br>Slide                                       |
| Position detection                                       | For proximity sensor  |
| Operating pressure MPa                                   | 0.15 ... 0.8 MPa  |
| Operating pressure                                       | 1.5 ... 8 bar   |
| Max. speed   | 0.8 m/s   |
| Repetition accuracy                                      | 0,3 mm  |
| Mode of operation  | double-acting   |
| Operating medium   | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium                       | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC                  | 0 - No corrosion stress   |
| PWIS conformity  | VDMA24364-B1/B2-L   |
| Ambient temperature                                      | 0 ... 60 °C   |
| Impact energy in end positions                           | 0.12 Nm   |
| Cushioning length  | 1.3 mm  |
| Max. force F <sub>y</sub>                                | 1,200 N   |
| Max. force F <sub>z</sub>                                | 1,200 N   |
| Max. torque M <sub>x</sub>                               | 18 Nm   |
| Max. torque M <sub>y</sub>                               | 12 Nm   |
| Max. torque M <sub>z</sub>                               | 12 Nm   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 51 N  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance    | 68 N  |
| Moving mass  | 299 g   |
| Product weight   | 744 g   |
| alternative connections                                  | See product drawing   |
| Mounting type  | with through hole   |
| Pneumatic connection                                     | M5  |
| Materials note   | Conforms to RoHS  |
| Material cover   | Wrought Aluminium alloy   |
| Material seals   | HNBR  |
| Material housing   | Wrought Aluminium alloy   |
| Material piston rod                                      | High alloy steel, non-corrosive   |