


solenoid valve

VUVG-B14-T32H-AZT-F-1R8L

Part number: 574244

FESTO



Data sheet

| Feature | Value |
|--|--|
| Valve function | 2x3/2 open/closed, monostable |
| Type of actuation | electrical |
| Valve size | 14 mm |
| Standard nominal flow rate | 510 ... 580 l/min |
| Operating pressure MPa | 0.15 ... 1 MPa |
| Operating pressure | 1.5 ... 10 bar |
| Design structure | Piston slide |
| Type of reset | Air spring |
| Authorisation | RCM Mark c UL us - Recognized (OL) |
| Protection class | IP65 with plug socket |
| Nominal size | 4.6 mm |
| Exhaust-air function | throttleable |
| Sealing principle | soft |
| Assembly position | Any |
| Manual override | detenting Pushing Covered |
| Type of piloting | Piloted |
| Pilot air supply | external |
| Overlap | Positive overlap |
| Pilot pressure MPa | 0.15 ... 0.8 MPa |
| Pilot pressure | 1.5 ... 8 bar |
| Suitability for vacuum | No |
| Switching time off | 25 ms |
| Switching time on | 9 ms |
| Duty cycle | 100 % |
| Max. positive test pulse with logic 0 | 700 µs |
| Max. negative test pulse with logic 1 | 900 µs |
| Characteristic coil data | 24 V DC: 1 W |
| Permissible voltage fluctuation | +/- 10 % |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Vibration resistance | Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6 |
| Restriction ambient and medium temperature | Without holding current reduction -5 - 50 °C |
| Shock resistance | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Medium temperature | -5 ... 60 °C |
| Pilot medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Ambient temperature | -5 ... 60 °C |

| Feature | Value |
|-----------------------|---------------------------------|
| Product weight | 89 g |
| Electrical connection | Via electrical connection plate |
| Mounting type | on manifold rail |
| Materials note | Conforms to RoHS |
| Material seals | HNBR NBR |
| Material housing | Wrought Aluminium alloy |