


manifold rail

VABM-L1-10HW-G18-9-GR

Part number: 573439

FESTO



Data sheet

| Feature | Value |
|-----------------------------------------|-------------------------------|
| Grid dimension | 10.5 mm |
| Assembly position | Any |
| Max. number of valve positions | 9 |
| Authorisation | c UL us - Recognized (OL) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| RSBP classification to CD-0033 | F1a |
| Cleanroom class | ISO class 6 |
| Storage temperature | -20 ... 60 °C |
| Product weight | 578 g |
| Auxiliary pilot air port 12/14 | M5 |
| Pilot exhaust port 82/84 | M5 |
| Pneumatic connection, port 1 | G1/8 |
| Pneumatic connection, port 2 | M7 |
| Pneumatic connection, port 3 | G1/8 |
| Pneumatic connection, port 4 | M7 |
| Pneumatic connection, port 5 | G1/8 |
| Materials note | Conforms to RoHS |
| Material manifold | Wrought Aluminium alloy |