

manifold rail

VABM-L1-10HW-G18-24-M-GR

Part number: 573932

FESTO



Data sheet

Feature	Value
Grid dimension	10.5 mm
Assembly position	Any
Max. number of valve positions	24
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
RSBP classification to CD-0033	F1a
Cleanroom class	ISO class 6
Storage temperature	-20 ... 60 °C
Product weight	1,148 g
Auxiliary pilot air port 12/14	M5
Pilot exhaust port 82/84	M5
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	M7
Pneumatic connection, port 3	G1/8
Pneumatic connection, port 4	M7
Pneumatic connection, port 5	G1/8
Materials note	Conforms to RoHS
Material manifold	Wrought Aluminium alloy