



# electric cylinder

## ESBF-...-63- -

Part number: 574090

FESTO



## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	63
Stroke	30 ... 1,200 mm
Piston rod thread	M16x1,5
Spindle diameter	25 mm
Max. angular deflection of piston rod +/-	0.4 deg
Based on the standard	ISO 15552
Assembly position	Any
Motor type	Servomotor
Position detection	For proximity sensor
Design structure	Electro-cylinder with ball screw
Spindle type	Ball screw spindle
Variants	Recommended for production facilities for the manufacture of lithium-ion batteries
Protection against torque/guide	with plain-bearing guide
Duty cycle	100 %
Corrosion resistance classification CRC	0 - No corrosion stress 2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III
RSBP classification to CD-0033	F1a
Cleanroom class	ISO class 7
Storage temperature	-20 ... 60 °C
Food-safe	See Supplementary material information
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 60 °C
Max. radial force at drive shaft	700 N
Max. feed force Fx	7,000 N
Reference value for working load, horizontal	700 kg
Reference value for working load, vertical	700 kg
Moving mass with 0 mm stroke	1,829 g
Additional mass factor per 10 mm of stroke	52 g
Basic weight for 0 mm stroke	3,163 g
Additional weight per 10 mm stroke	87 g
Mounting type	with internal (female) thread or accessories
Interface code, actuator	D60
Materials note	Conforms to RoHS
Material cover	Die-cast aluminium, coated
Material piston rod	High alloy steel, non-corrosive
Material screws	Galvanised steel
Material spindle nut	Roller bearing steel
Material spindle	Roller bearing steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy