



one-way flow control valve VFOH-LE-A-G14-Q10

Part number: 578801

FESTO



Data sheet

Feature	Value
Valve function	One-way flow control function for exhaust air
Pneumatic connection, port 1	QS-10
Pneumatic connection, port 2	G1/4
Type of actuation	manual
Adjusting element	External hex
Mounting type	Threaded
Standard nominal flow rate in flow control direction	520 l/min
Standard nominal flow rate in non-return direction	345 ... 535 l/min
Ambient temperature	0 ... 150 °C
Assembly position	Any
Operating pressure complete temperature range	0.2 ... 10 bar
Standard flow rate in flow control direction 0.6->0 MPa (6->0 bar, 87->0 psi)	840 l/min
Standard flow rate in non-return direction at 0.6->0 MPa (6->0 bar, 87->0 psi)	635 ... 790 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B2-L
Storage temperature	-10 ... 150 °C
Medium temperature	0 ... 150 °C
Nominal tightening torque	5 Nm
Tolerance for nominal tightening torque	± 10 %
Product weight	48 g
Materials note	Conforms to RoHS
Material seals	FPM
Material hollow bolt	Wrought Aluminium alloy
Material release ring	Nickel-plated brass
Material adjusting screw	High alloy steel, non-corrosive
Material swivel fitting	Brass Nickel plated