


handling module EHMZ-DGEA-18-TB-KF- -

Part number: 8004625
Product to be discontinued

FESTO

Type to be discontinued. Available until 2024. See Support Portal for alternative products.



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Effective diameter of drive pinion	25.78 mm
Working stroke	50 ... 800 mm
Toothed-belt stretch	0.037 %
Toothed-belt pitch	3 mm
Assembly position	Vertical
Design structure	Electromechanical linear module With toothed belt
Position detection	For proximity sensor
Max. speed	3 m/s
Repetition accuracy	±0,05 mm
Duty cycle	100 %
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 90 %
Protection class	IP20
Ambient temperature	5 ... 45 °C
Max. feed force F _x	230 N
Feed constant	81 mm/U
Materials note	Conforms to RoHS