


push-in L-connector NPQH-L-Q6-E-P10

Part number: 578271

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal size | 5 mm |
| Tubing insertion depth | 15.8 mm |
| Assembly position | Any |
| Design | L-shape |
| Container size | 10 |
| Design structure | Push/pull principle |
| Operating pressure for entire temperature range | -0.095 ... 2 MPa |
| Operating pressure complete temperature range | -0.95 ... 20 bar |
| Operating pressure for entire temperature range | -13.775 ... 290 psi |
| Note on operating pressure | Water: max. 0.6 MPa at 0 - 50 °C |
| Certificate issuing department | NSF C0523185 |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water (liquid, free of ice) |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 3 - High corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Cleanroom class | ISO class 4 |
| Food-safe | See declaration of conformity NSF/ANSI 169 |
| Ambient temperature | 0 ... 150 °C |
| Product weight | 17.2 g |
| Pneumatic connection, port 1 | For tubing outside diameter 6 mm |
| Pneumatic connection, port 2 | For tubing outside diameter 6 mm |
| Materials note | Conforms to RoHS |
| Material housing | Brass, chemically nickel-plated |
| Guard ring material | PEI |
| Material release ring | Brass, chemically nickel-plated |
| Material of tubing seal | FPM |
| Material of tube retaining claw | High alloy steel, non-corrosive |
| Thrust ring material | PEI |