



solenoid valve

VUVS-LT30-M32C-MZD-G38-F8-1B2

Part number: 8036677

FESTO



Data sheet

| Feature | Value |
|---|--|
| Valve function | 3/2 closed, monostable |
| Type of actuation | electrical |
| Valve size | 31 mm |
| Standard nominal flow rate | 1,600 l/min |
| Operating pressure MPa | 0.1 ... 1 MPa |
| Operating pressure | 1 ... 10 bar |
| Design structure | Poppet seat |
| Type of reset | mechanical spring |
| Authorisation | c UL us - Recognized (OL) |
| Protection class | IP65 with plug socket to IEC 60529 |
| Nominal size | 7.9 mm |
| Exhaust-air function | throttleable |
| Sealing principle | soft |
| Assembly position | Any |
| Manual override | detenting Pushing |
| Type of piloting | Piloted |
| Pilot air supply | external |
| Flow direction | non reversible |
| Overlap | Underlap |
| Pilot pressure MPa | 0.25 ... 1 MPa |
| Pilot pressure | 2.5 ... 10 bar |
| b value | 0.4 |
| C value | 6 l/sbar |
| Switching time off | 32 ms |
| Switching time on | 13 ms |
| Duty cycle | 100 % |
| Max. positive test pulse with logic 0 | 2,000 µs |
| Max. negative test pulse with logic 1 | 3,600 µs |
| Characteristic coil data | 24 V DC: 3.3 W |
| Permissible voltage fluctuation | +/- 10 % |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Vibration resistance | Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| Medium temperature | -10 ... 60 °C |
| Pilot medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Ambient temperature | -10 ... 60 °C |
| Product weight | 359 g |
| Electrical connection | Plug pattern type B to EN 175301-803 |

| Feature | Value |
|-------------------------------|---|
| | To industry standard (11 mm) |
| Mounting type | on manifold rail with through hole Optional |
| Scavenging orifice connection | Non-ducted |
| Pilot exhaust port 82 | M5 |
| Pilot air port 12 | G1/8 |
| Pneumatic connection, port 1 | G3/8 |
| Pneumatic connection, port 2 | G3/8 |
| Pneumatic connection, port 3 | G3/8 |
| Materials note | Conforms to RoHS |
| Material seals | HNBR NBR TPE-U(PU) |
| Material housing | Die-cast aluminium, painted |
| Material Piston slide | Wrought Aluminium alloy |
| Material screws | Galvanised steel |