


angle seat valve

VZXA-B-TS6-32-M2-V13T-25-M-90-26-V4

Part number: 8060535

FESTO

Modular, pneumatically actuated angle seat valve in stainless steel.
Under seat version, safety position closed, G thread, nominal width DN32.



Data sheet

| Feature | Value |
|--|--|
| Design structure | Poppet valve with diaphragm actuator |
| Type of actuation | pneumatic |
| Assembly position | Any |
| Mounting type | Line installation |
| Line connection | G1¼ threaded collar to DIN ISO 228 |
| Valve function | 2/2 |
| Flow direction | non reversible |
| Pressure of medium | 0 ... 2.5 MPa |
| Medium pressure | 0 ... 25 bar |
| Type of reset | mechanical spring |
| Type of piloting | With external control |
| Pneumatic connection | Female thread G1/8 |
| Operating pressure MPa | 0.5 ... 0.7 MPa |
| Operating pressure | 5 ... 7 bar 72.5 ... 101.5 psi |
| Medium | Vapour Mineral oil-based hydraulic oil Inert gases Mineral oil Water Filtered compressed air, degree of filtration 200 µm Neutral fluids |
| Flow direction | Below valve seat, for gaseous and liquid media |
| Control of the medium | On/off operation |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Max. viscosity | 600 mm ² /s |
| Medium temperature | -10 ... 180 °C |
| Ambient temperature | 0 ... 60 °C |
| Flow rate Kv | 33.1 m ³ /h |
| Outdoor use | C1 - weather protected locations of use |
| Materials note | Conforms to RoHS |
| PWIS conformity | VDMA24364 zone III |
| Material process valve housing | Stainless steel casting |
| Material number, process valve housing | 1.4409 |
| Material seals | NBR |
| Material spindle seal | PTFE |
| Material seat seal | PTFE |
| Product weight | 7,110 g |
| Authorisation | CRN |
| CE mark (see declaration of conformity) | to EU directive pressure devices |
| UKCA marking (see declaration of conformity) | UK regulation for pressure equipment |
| Certificate issuing department | TÜV 968/V 1039.01/20 |
| Safety Integrity Level (SIL) | SIL 2 |

| Feature | Value |
|---|---------------------------------|
| Probability of Failure per Hour in [1/h]. | 1.36E-07 |
| PFD (Probability of Failure on Demand) | 5.95E-04 |
| Actuator size | 90 mm |
| Stroke | 26 mm |
| Control function | Closed via spring force, NC |
| Position detection | With mechanical indicator |
| Material drive housing | Stainless steel casting |
| Material number, actuator housing | 1.4408 |
| Storage temperature | -10 ... 60 °C |
| Protection class | IP65 IP67 |
| Material piston rod | High alloy steel, non-corrosive |
| Material cover | Stainless steel casting |