



guide axis ELFC-KF-32-500

Part number: 8062800

FESTO



Data sheet

Feature	Value
Working stroke	500 mm
Size	32
Stroke reserve	0 mm
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Guide
Max. acceleration	250 m/s ²
Max. speed	1.5 m/s
Duty cycle	100 %
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
RSBP classification to CD-0033	F1a
Cleanroom class	ISO class 7
Protection class	IP40
Ambient temperature	0 ... 50 °C
Area moment of inertia 2nd degree Iy	38E+03 mm ⁴
Area moment of inertia 2nd degree Iz	45E+03 mm ⁴
Max. force Fy	150 N
Max. force Fz	300 N
Max. torque Mx	1.3 Nm
Max. torque My	1.1 Nm
Max. torque Mz	1.1 Nm
Torsional mass moment of inertia It	1.77E+03 mm ⁴
Displacement force	2 N
Fy with theoretical service life of 100 km (from a guide perspective only)	552 N
Fz with theoretical service life of 100 km (from a guide perspective only)	1,104 N
Mx with theoretical service life of 100 km (from a guide perspective only)	5 Nm
My with theoretical service life of 100 km (from a guide perspective only)	4 Nm
Mz with theoretical service life of 100 km (from a guide perspective only)	4 Nm
Moving mass	61 g
Additional weight per 10 mm stroke	11 g
Material of end caps	Die-cast aluminium, painted
Material of profile	Anodised wrought aluminium alloy
Materials note	Conforms to RoHS
Material cover tape	High alloy steel, non-corrosive
Material cover	Die-cast aluminium, painted
Material guide slide	Steel
Material guide rail	Steel
Material slide	Aluminium die cast