

semi-rotary drive

DFPD-N-240-RP-120-RD-F0710

Part number: 8068202

FESTO

double-acting, rack and pinion design, connection pattern to NAMUR VDI/VDE 3845 for mounting solenoid valves, position sensors and positioners, standard connection to fitting ISO 5211, NPT control air connection thread type.



Data sheet

| Feature | Value |
|--|--|
| Size of actuator | 240 |
| Flange hole pattern | F0710 |
| Swivel angle | 120 deg |
| End-position adjustment range at 0° | -5 ... 5 deg |
| End-position adjusting range at nominal swivel angle | -5 ... 5 deg |
| Shaft connection depth | 24 mm |
| Fitting connection conforms to standard | ISO 5211 |
| Assembly position | Any |
| Mode of operation | double-acting |
| Design structure | Rack and pinion |
| Closing direction | right-closing |
| Valve connection conforms to standard | VDI/VDE 3845 (NAMUR) |
| Connection for positioner and position sensor conforms to standard | VDI/VDE 3845 size AA 2 |
| Component suitable for safety functions | Safety device |
| Safety function | The safety function consists of the actuator switching to the specified safety switching position. This switching movement is achieved by pressurising the corresponding pressure chamber with compressed air. The value of the torque generated depends on the differential pressure between the two pressure chambers separated by the piston. |
| Safety Integrity Level (SIL) | Product can be used in SRP/CS up to SIL 2 low demand Up to SIL 3 in redundant architecture up to SIL 1 high demand mode |
| Certified for safety function to ISO 13849 and IEC 61508 (SIL) | Product can be used in SRP/CS up to SIL 2 low demand up to SIL 1 high demand mode Up to SIL 3 in redundant architecture |
| Operating pressure MPa | 0.2 ... 0.8 MPa |
| Operating pressure | 2 ... 8 bar 29 ... 116 psi |
| Nominal operating pressure | 0.55 MPa 5.5 bar |
| Nominal operating pressure (psi) | 79.75 psi |
| Maritime classification | see certificate |
| CE mark (see declaration of conformity) | to EU directive explosion protection (ATEX) |
| UKCA marking (see declaration of conformity) | To UK EX instructions |
| Explosion protection certification outside the EU | EPL Db (GB) EPL Gb (GB) |
| Certificate issuing department | DNV TAP00001CE German Technical Control Board (TÜV) Rheinland 968/V 1106.01/2023 |
| ATEX category Gas | II 2G |
| ATEX category Dust | II 2D |
| Explosion ignition protection type Gas | Ex h IIC T4 Gb X |

| Feature | Value |
|---|--|
| Explosion ignition protection type Dust | Ex h IIIC T105°C Db X |
| Explosion-proof ambient temperature | -20°C ≤ Ta ≤ +80°C |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Pressure dew point 10°C below ambient temperature/temperature of medium Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 ... 60 °C |
| Ambient temperature | -20 ... 80 °C |
| Torque at rated operating pressure and 0° rotation angle | 234.3 Nm |
| Torque at nominal operating pressure with 90° swivel angle | 234.3 Nm |
| Note about the torque | The operating torque of the actuator must not be higher than the maximum permissible torque listed in ISO 5211, with reference to the size of the mounting flange and of the coupling. |
| Mean Time to Dangerous Failure (MTTFd) | 1126 years |
| Probability of Failure per Hour in [1/h]. | 1.01E-07 |
| PFD (Probability of Failure on Demand) | 1.42E-03 |
| Air consumption at 0.6 MPa (6 bar, 87 psi) per cycle 0°-nominal swivel angle-0° | 24.5 l |
| Product weight | 10,939 g |
| Shaft connection | T22 |
| Pneumatic connection | 1/4 NPT |
| Materials note | Conforms to RoHS |
| Material of connecting plate | Anodised wrought aluminium alloy |
| Material cover | Die-cast aluminium, coated |
| Material seals | NBR |
| Material housing | Anodised wrought aluminium alloy |
| Material piston | Aluminium die cast |
| Material bearing | POM |
| Material cam | Steel |
| Material screws | High alloy steel, non-corrosive |
| Material shaft | Steel, nickel-plated |