


sub-base VABS-P12-S-M5-P3

Part number: 8068637

FESTO



Data sheet

Feature	Value
Width	25 mm
Assembly position	Any
Special characteristics	Oxygen-compatible to DIN EN 1797
Max. number of valve positions	1
Operating pressure	0 ... 1.7 bar
Standard nominal flow rate	>= 27 l/min
Standard nominal flow rate 2-3	>= 28 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [5:3:1] Inert gases Oxygen
Note on operating and pilot medium	Lubricated operation not possible Maximum particle size: 5 µm
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Storage temperature	-20 ... 70 °C
Medium temperature	-20 ... 60 °C
Relative air humidity	0 - 70 % non-condensing
Protection class	IP00
Note on degree of protection	in assembled condition
Ambient temperature	-20 ... 70 °C
Product weight	55 g
Mounting type	with through hole
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M5
Pneumatic connection 2S	M5
Pneumatic connection, port 3	M5
Pneumatic connection, port 5	M5
Materials note	Conforms to RoHS
Material of connecting plate	Anodised wrought aluminium alloy