

mini slide DGST-6-40-E1A

Part number: 8078831

FESTO



Data sheet

Feature	Value
Stroke	40 mm
Piston diameter	6 mm
Operating mode of drive unit	Yoke
Cushioning	Elastomer cushioning, at both ends, stroke not adjustable
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	twin piston Yoke Piston rod Slide
Position detection	For proximity sensor
Operating pressure MPa	0.15 ... 0.8 MPa
Operating pressure	1.5 ... 8 bar 21.75 ... 116 psi
Max. speed	0.5 m/s
Repetition accuracy	≤ 0,3 mm
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Impact energy in end positions	0.012 J
Cushioning length	0.9 mm
Max. force F _y	260 N
Max. force F _z	260 N
Max. torque M _x	1.2 Nm
Max. torque M _y	1.2 Nm
Max. torque M _z	1.2 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	25 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	34 N
Moving mass	73 g
Product weight	140 g
Mounting type	with through hole
Pneumatic connection	M3
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	HNBR
Material of guide	POM High alloy steel TPE-E
Material housing	Wrought Aluminium alloy
Material piston rod	High alloy steel, non-corrosive