


cantilever axis

ELCC-TB-KF-60-200-0H-P0-CR

Part number: 8082386

FESTO



Data sheet

Feature	Value
Effective diameter of drive pinion	30.558 mm
Working stroke	200 mm
Size	60
Stroke reserve	0 mm
Toothed-belt pitch	3 mm
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Electromechanical Cantilever axis
Max. acceleration	50 m/s ²
Max. speed	5 m/s
Repetition accuracy	±0,05 mm
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
Protection class	IP20
Ambient temperature	-10 ... 60 °C
Area moment of inertia 2nd degree Iy	240.6E+03 mm ⁴
Area moment of inertia 2nd degree Iz	304.21E+03 mm ⁴
Max. drive torque	5.2 Nm
Max. force Fy	4,216 N
Max. force Fz	4,119 N
Max. torque Mx	36 Nm
Max. torque My	293 Nm
Max. torque Mz	288 Nm
Max. feed force Fx	300 N
Mass moment of inertia JH per metre of stroke	8.9 kgcm ²
Mass moment of inertia JL per kg of working load	2.3 kgcm ²
Mass moment of inertia, JO	5.9 kgcm ²
Feed constant	96 mm/U
Reference value, running performance	5,000 km
Lubrication interval, distance dependent	1,000 km
Moving mass with 0 mm stroke	1,636 g
Additional mass factor per 10 mm of stroke	38 g
Basic weight for 0 mm stroke	4,146 g
Additional weight per 10 mm stroke	38 g
Material of end caps	Anodised wrought aluminium alloy
Material of profile	Anodised wrought aluminium alloy
Materials note	Conforms to RoHS
Material drive head	Anodised wrought aluminium alloy
Material guide rail	Rolled steel, Corrotect coated
Material housing	High alloy steel, non-corrosive
Material slide	Cast aluminium, anodised
Material toothed belt clamping piece	Anodised wrought aluminium alloy
Material toothed belt	polychloroprene with glass cord and nylon coating