


rotary drive unit ERMS-32-

Part number: 8087809

FESTO



Exemplary representation



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	32
Design structure	Electromechanical rotary drive With integrated drive With integrated gearing
Assembly position	Any
Mounting type	with internal (female) thread
Rotation angle	90° 180°
Gear unit ratio	7:1
Max. speed	100 1/min
Max. speed at 90°	100 1/min
Torsional backlash	0.2 deg
Repetition accuracy	±0,1 °
Position detection	Motor encoder
Max. axial force	450 N
Max. radial force	550 N
Permissible mass moment of inertia	0.0164 kgm ²
Product weight	2,304 g
Stepper angle at full step	1.8 deg
Stepper angle tolerance	±5 %
Duty cycle	100 %
Power supply, type of connection	Plug
Power supply, connection technology	M12x1, T-coded to EN 61076-2-111
Power supply, number of pins/wires	4
Logic interface, connection type	Plug
Logic interface, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Logic interface, number of poles/wires	8
Logic interface, connection pattern	00992264
Max. line length	15 m outputs 15 m inputs 20 m with IO-Link operation
Nominal voltage DC	24 V
Nominal current	5.3 A
Nominal motor current	5 A
Max. current consumption	5.3 A
Permissible voltage fluctuation	+/- 15 %
Number of digital logic inputs	2
Logic input characteristics	configurable Not electrically isolated
Specification, logic input	Based on IEC 61131-2, type 1
Logic input working range	24 V
Input circuit logic	NPN (negative switching) PNP (positive-switching)
Number of 24 V DC digital logic outputs	2

Feature	Value
Digital logic output characteristics	configurable Not electrically isolated
Max. current, digital logic outputs	100 mA
Switching logic, outputs	NPN (negative switching) PNP (positive-switching)
IO-Link, SIO mode support	Yes
IO-Link, protocol	Device V 1.1
IO-Link, communication mode	COM3 (230.4 kbd)
IO-Link, port type	A
IO-Link, number of ports	1
IO-Link, process data width OUT	2 Byte
IO-Link, process data content OUT	Move in 1 bit Move out 1 bit Quit Error 1 bit Move Intermediate 1 bit
IO-Link, process data width IN	2 Byte
IO-Link, process data content IN	State In 1 bit State Out 1 bit State Move 1 bit State Device 1 bit State Intermediate 1 bit
IO-Link, Service data contents IN	32 bit Force 32 bit Position 32 bit Speed
IO-Link, minimum cycle time	1 ms
IO-Link, data memory required	0.5 Kilobyte
IO-Link, connection technology	Plug
Parameters configuring interface	IO-Link User interface
Insulation protection class	B
Motor type	Stepper motor
Rotor position sensor	Absolute single turn encoder
Rotary position encoder measuring principle	Magnetic
Rotor position encoder resolution	16 Bit
Referencing	Fixed stop block positive Fixed stop block negative
Protective function	Temperature monitoring
Additional functions	User interface Integrated end-position sensing
Display	LED
Ready status display	LED
Angular acceleration	$\leq 140 \text{ rad/s}^2$
Authorisation	RCM Mark
KC mark	KC-EMV
CE mark (see declaration of conformity)	to EU directive for EMC in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Peak torque	5.6 Nm
Interface code, base	E8-55
Protection class	IP40
Safety class	III
Storage temperature	-20 ... 60 °C
Ambient temperature	0 ... 50 °C
Note on ambient temperature	Above an ambient temperature of 30 °C, the power must be reduced by 2% per K.
Relative air humidity	0 - 85 %
Vibration resistance	Transport application test with severity level 1 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 1 in accordance with FN 942017-5 and EN 60068-2-27

Feature	Value
PWIS conformity	VDMA24364 zone III
Materials note	Conforms to RoHS
Material flange	Wrought aluminium alloy, anodised
Material housing	Anodised wrought aluminium alloy
Speed "Speed press"	2 m/s
Max. current consumption, logic	0.3 A
Maintenance interval	Life-time lubrication