


compact cylinder ADN-S-32-5-A-P

Part number: 8091452

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 5 mm |
| Piston diameter | 32 mm |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Mode of operation | double-acting |
| Piston-rod end | Male thread |
| Design structure | Piston Piston rod |
| Variants | Single-ended piston rod |
| Operating pressure MPa | 0.06 ... 1 MPa |
| Operating pressure | 0.6 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | 0 ... 60 °C |
| Impact energy in end positions | 0.26 J |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 415 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 483 N |
| Moving mass with 0 mm stroke | 31 g |
| Additional mass factor per 10 mm of stroke | 9 g |
| Basic weight for 0 mm stroke | 107 g |
| Additional weight per 10 mm stroke | 36 g |
| Mounting type | with through hole with internal (female) thread with accessories Optional |
| Pneumatic connection | M5 |
| Materials note | Conforms to RoHS |
| Material cover | Anodised wrought aluminium alloy |
| Material of dynamic seals | NBR |
| Material housing | Anodised wrought aluminium alloy |
| Material piston rod | High alloy steel, non-corrosive |