

servo drive CMMT-ST-C8-1C-PN-S0

Part number: 8084004

★ Core product range

Product to be discontinued

Type to be discontinued. Available until 2024. See Support Portal for alternative products.

FESTO



Data sheet

Feature	Value
Mounting type	Mounting plate, bolted with top-hat rail
Assembly position	Free convection Vertical
Product weight	350 g
Display	LED green/yellow/red
Authorisation	RCM Mark c UL us - Listed (OL)
KC mark	KC-EMV
CE mark (see declaration of conformity)	to EU directive for EMC to EU directive for machinery in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK instructions for machines To UK RoHS instructions
Certificate issuing department	TÜV Rheinland 01/205/5696.00/19 UL E331130 TÜV Rh. UK 01/205U/5696.00/22
Storage temperature	-25 ... 55 °C
Ambient temperature	0 ... 50 °C
Note on ambient temperature	Observe derating with regard to mounting clearance and output current
Relative air humidity	5 - 90 % non-condensing
Max. installation height	2,000 m
Protection class	IP20
Safety class	III
Overvoltage category	I
Degree of contamination	2
Materials note	Conforms to RoHS
PWIS conformity	VDMA24364 zone III
Nominal voltage, load supply DC	24 ... 48 V
Permissible range, load supply	-15 % / +15 %
Max. intermediate circuit voltage, DC	60 V
Nominal DC voltage, logic power supply	24 V
Permissible range, logic voltage	± 15 %
Current consumption, logic power supply without clamping brake	1 A
Current consumption for logic supply with locking brake	2 A
Output voltage range AC	0 V up to input voltage
Nominal output current	8 A
Effective nominal current per phase	8 A
Effective peak current per phase	10 A
Max. peak current duration	3 s
Nominal controller power	300 W

Feature	Value
Peak power	400 W
Output frequency	0 ... 20,000 Hz
Max. length of motor cable without external mains filter	25 m
Max. output current of holding brake	1 A
Max. voltage drop from logic supply to brake output	1 V
Controller operating mode	Cascade controller P position controller PI speed controller PI current regulator for F or M Profile operation with record and direct mode Interpolated mode via fieldbus Synchronised operating modes Homing Setting-up Autotuning Open-loop operation
Operating mode	Field-oriented closed-loop control Position resolution 24 bit/U Sampling rate 20 kHz Pulse-width modulation with 20 kHz Real-time data acquisition 2x Input-Capture (x, v, F) 2x Output-Trigger (x, v, F) 1x position sensor input
Adjustable current reduction	Using software
Protective function	I ² t monitoring Temperature monitoring Current monitoring Voltage failure detection Drag error monitoring Software end-position detection
Nominal current adjustment	Using software
Ethernet interface, function	Parameterisation and commissioning
Ethernet interface, protocol	TCP/IP
Fieldbus interface, protocol	PROFINET IRT PROFINET RT
Fieldbus coupling	PROFINET
Communications profile	PROFIdrive
Process interface	AC1: Adj.-Speed Drives AC3: Drive w. Positioning Func AC4: Synchr. Servo Application
Fieldbus interface, transmission rate	100 Mbit/s
Fieldbus interface, type of connection	2x socket
Fieldbus interface, connection technology	RJ45
Encoder interface, function	BiSS-C Incremental encoder
Number of digital logic inputs	6
Input circuit logic	NPN (negative switching) PNP (positive-switching)
Logic input characteristics	Freely configurable to a given extent Safety inputs in some cases Not electrically isolated
Specification, logic input	Based on IEC 61131-2, type 3
Logic input working range	-3 ... 30 V
Number of high-speed logic inputs	2
Time resolution of high-speed logic inputs	1 µs
Number of 24 V DC digital logic outputs	2
Switching logic, outputs	NPN (negative switching) PNP (positive-switching)
Digital logic output characteristics	configurable Not electrically isolated

Feature	Value
Max. current, digital logic outputs	100 mA
Number of high-speed switching outputs	2
Time resolution of high-speed switching outputs	1 µs
Number of floating switching outputs	1
Max. current of the floating switching outputs	100 mA
Safety function	Safe torque off (STO) Safe stop 1 (SS1-time controlled)
Safety Integrity Level (SIL)	STO / SIL 2 / SILCL 2 (EC motor without diagnostics) STO / SIL 3 / SILCL 3 (stepper motor/EC motor with diagnostics)
Performance level (PL)	STO / cat. 3 PLd (EC motor without diagnostics) STO / cat. 3, PLe (stepper motor/EC motor with diagnostics)
Diagnostic coverage	STO: 87% (EC motor without diagnostics) STO / 90% (stepper motor) STO: 92% (EC motor with diagnostics)
Hardware fault tolerance	1
Proof test interval	STO / 20 a (stepper motor/EC motor without diagnostics)
Number of safe 2-pin inputs	1
Number of diagnostic outputs	1