

# parallel kit EAMM-U-110-S95-90GA-207

Part number: 8105907

FESTO



## Data sheet

Feature	Value
Size	110
Assembly position	Any
Max. speed	5,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	799 kgmm <sup>2</sup>
No-load driving torque	0.3 Nm
Transferable torque	9.5 Nm
Product weight	6,900 g
Interface code, actuator	S95
Interface code, motor in	90GA
Materials note	Conforms to RoHS