



# air gap sensor SOPA-CM3H-R1-HQ6-PNLK-VB-M12

Part number: 8093822

FESTO



## Data sheet

Feature	Value
Authorisation	RCM Mark c UL us - Recognized (OL)
CE mark (see declaration of conformity)	to EU directive for EMC in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC mark	KC-EMV
Materials note	Conforms to RoHS
Detected variable	Distance
Measuring principle	pneumatic
Sensing range	20 ... 200 µm
Operating pressure	4 ... 7 bar
Supply pressure	0.8 ... 1.6 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Ambient temperature	0 ... 50 °C
Repetition accuracy in ± µm	2.5 µm
Switch output	PNP/NPN, switchable
Switching function	Window comparator Threshold value with variable hysteresis
Switching element function	N/C or N/O contact, switchable
Max. output current	100 mA
Analogue output	0 - 10 V
Start value distance characteristic curve	0 µm
End value distance characteristic curve	300 µm
Rise time	22 ms
Min. load resistance, voltage output	20 kOhm
Short circuit strength	Yes
Protocol	IO-Link
IO-Link, protocol	Device V 1.1
IO-Link, profile	Smart sensor profile
IO-Link, function classes	Process Data Variable (PDV) Identification diagnosis Teach channel Switching signal channel (SSC)
IO-Link, communication mode	COM2 (38,4 kBaud)
IO-Link, SIO mode support	Yes
IO-Link, port type	A
IO-Link, process data width OUT	0 Byte
IO-Link, process data width IN	2 Byte
IO-Link, process data content IN	2-bit SSC (distance monitoring) 1-bit SSC (supply pressure monitoring) 10-bit PDV (distance)
IO-Link, Service data contents IN	14-bit supply pressure

<b>Feature</b>	<b>Value</b>
IO-Link, minimum cycle time	3 ms
IO-Link, data memory required	< 500 Byte
Operating voltage range DC	22.8 ... 26.4 V
Max. current consumption	550 mA
Polarity protected	for all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	5
Electrical connection 1, type of mounting	Screw lock
Mounting type	with through hole with top-hat rail Optional
Pneumatic connection	QS-6
Product weight	630 g
Material housing	PA-reinforced
Type of display	Illuminated LCD, multicoloured
Setting options	IO-Link Teach-In Via display and buttons
Protection against manipulation	Electronic locking
Protection class	IP65
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-C1-L