


guided drive DFM-25-50-P-A-GF-F1A

Part number: 8118866

FESTO

The proximity switch, type SMTSO-8E, can be used with this product with stroke lengths equal to or greater than 50 mm. The corresponding mounting kit, type SMB-8E, is mounted inwardly or outwardly.



Data sheet

Feature	Value
Centre of gravity distance from working load to yoke plate	50 mm
Stroke	50 mm
Piston diameter	25 mm
Operating mode of drive unit	Yoke
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Guide	Plain-bearing guide
Design structure	Guide
Position detection	For proximity sensor
Variants	Recommended for production facilities for the manufacture of lithium-ion batteries
Operating pressure MPa	0.15 ... 1 MPa
Operating pressure	1.5 ... 10 bar
Max. speed	0.8 m/s
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
RSBP classification to CD-0033	F1a
Cleanroom class	ISO class 8
Ambient temperature	-20 ... 80 °C
Impact energy in end positions	0.3 Nm
Max. force Fy	810.7 N
Max. force Fy static	810.7 N
Max. force Fz	810.7 N
Max. force Fz static	810.7 N
Max. torque Mx	27.56 Nm
Max. torque Mx static	27.56 Nm
Max. torque My	19.46 Nm
Max. torque My static	19.46 Nm
Max. torque Mz	19.46 Nm
Max. torque Mz static	19.46 Nm
Max. permissible torque load Mx as a function of the stroke	5.26 Nm
Max. useful load as a function of the stroke at defined distance xs	115 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	247 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	295 N
Moving mass	793 g
Product weight	1,635 g
alternative connections	See product drawing
Pneumatic connection	G1/8

Feature	Value
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	NBR
Material housing	Wrought Aluminium alloy
Material piston rod	High alloy steel, non-corrosive