


adapter kit DADG-AK-F9-2

Part number: 8104804

FESTO



Data sheet

Feature	Value
Size	2
Based on the standard	VDI/VDE 3847-2
Assembly position	Any
Operating pressure MPa	0.2 ... 0.8 MPa
Operating pressure	2 ... 8 bar 29 ... 116 psi
Nominal operating pressure	0.6 MPa 6 bar
Nominal operating pressure (psi)	87 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Pressure dew point 10°C below ambient temperature/temperature of medium Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364 zone III
Ambient temperature	-20 ... 80 °C
Product weight	418 g
Materials note	Conforms to RoHS
Material adapter	High alloy steel, non-corrosive
Material adapter plate	Anodised wrought aluminium alloy
Material seals	NBR
Material screws	High alloy steel, non-corrosive