


parallel gripper DHPL-32-70-P-A

Part number: 8112223

FESTO



Data sheet

Feature	Value
Size	32
Total stroke	70 mm
Stroke per gripper jaw	35 mm
Max. replacement accuracy	≤ 0.2 mm
Max. angular gripper jaw backlash ax,ay	≤ 0.12 deg
Max. gripper jaw backlash Sz	≤ 0.066 mm
Rotationally symmetrical	≤ 0.2 mm
Repetition accuracy, gripper	≤ 0.03 mm
Number of gripper fingers	2
Assembly position	Any
Mode of operation	double-acting
Cushioning	P: Flexible cushioning rings/plates at both ends
Gripper function	Parallel
Design structure	Rack and pinion
Guide	Plain-bearing guide
Position detection	For proximity sensor
Total gripping force at 0.6 MPa (6 bar, 87 psi), opening	760 N
Total gripping force at 0.6 MPa (6 bar, 87 psi), closing	570 N
Operating pressure MPa	0.15 ... 0.8 MPa
Operating pressure	1.5 ... 8 bar 21.75 ... 116 psi
Max. operating frequency of gripper	≤ 1 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	112 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	209 ms
Max. mass per external gripper finger	498 g
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Protection class	IP54
Ambient temperature	-10 ... 60 °C
Gripping force per gripper jaw at 0.6 MPa (6 bar, 87 psi) opening	380 N
Gripping force per gripper jaw at 0.6 MPa (6 bar, 87 psi) closing	285 N
Mass moment of inertia	101.8 ... 176.1 kgcm ²
Max. force on gripper jaw Fz static	750 N
Max. torque at gripper Mx static	18 Nm
Max. torque at gripper My static	18 Nm
Max. torque at gripper Mz static	18 Nm
Maintenance interval	Life-time lubrication
Product weight	2,634 g
Mounting type	Direct mounting via threads with through hole Optional
Pneumatic connection	G1/8
Materials note	Conforms to RoHS

Feature	Value
Material cover cap	Anodised wrought aluminium alloy
Material cover	Anodised wrought aluminium alloy
Material end plate	Anodised wrought aluminium alloy
Material housing	Anodised wrought aluminium alloy
Material gripper jaws	Anodised wrought aluminium alloy
Material piston seal	TPE-U(PU)
Material piston rod	High alloy steel, non-corrosive
Material o-ring	NBR
Material screws	Galvanised steel
Gear rack material	High alloy steel, non-corrosive
Gear material	Sintered bronze