


axial kit EAMM-A-D32-50GA

Part number: 8117072

FESTO



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	6.5 Nm
Product weight	446 g
Interface code, actuator	D32
Interface code, motor in	50GA
Materials note	Conforms to RoHS