


radial gripper DHRC-16-A-S-NO

Part number: 8128721

FESTO



Data sheet

Feature	Value
Size	16
Max. replacement accuracy	≤ 0.2 mm
Max. opening angle	180 deg
Rotationally symmetrical	≤ 0.2 mm
Repetition accuracy, gripper	≤ 0.1 mm
Number of gripper fingers	2
Drive system	pneumatic
Assembly position	Any
Mode of operation	single-acting open
Gripper function	radial
Gripper force back-up	On opening
Design structure	Connection direction on the side guided motion sequence
Position detection	For proximity sensor
Operating pressure MPa	0.2 ... 0.8 MPa
Operating pressure	2 ... 8 bar 29 ... 116 psi
Max. operating frequency of gripper	≤ 2 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	42 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	21 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 60 °C
Total gripping torque at 0.6 MPa (6 bar, 87 psi) closing	50.3 Ncm
Mass moment of inertia	0.134 kgcm ²
Max. force on gripper jaw Fz static	60 N
Max. torque at gripper Mx static	2 Nm
Max. torque at gripper My static	1 Nm
Max. torque at gripper Mz static	2 Nm
Product weight	112.5 g
Mounting type	Direct mounting via through-holes Direct mounting via threads With through-hole and dowel pin With internal thread and dowel pin Optional
Pneumatic connection	M3
Materials note	Conforms to RoHS
Material cover cap	Anodised wrought aluminium alloy
Material housing	Anodised wrought aluminium alloy
Material gripper jaws	High alloy steel