


# parallel kit EAMM-U-60-D40-60P-61

Part number: 8164735

FESTO



## Data sheet

Feature	Value
Size	60
Assembly position	Any
Gear unit ratio	1:1
Max. speed	6,000 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	26.7 kgmm <sup>2</sup>
No-load driving torque	0.07 Nm
Transferable torque	3 Nm
Product weight	926 g
Interface code, actuator	D40B
Interface code, motor in	60P
Materials note	Conforms to RoHS