

manifold sub-base VABX-A-P-EL-E12-MS3-SHUH

Part number: 8188449
New

FESTO

Data sheet

Feature	Value
Max. number of solenoid coils	32
Dimensions W x L x H	45 mm x 104,3 mm x 53,3 mm
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
Authorisation	RCM Mark
KC mark	KC-EMV
CE mark (see declaration of conformity)	to EU directive for EMC in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-20 ... 70 °C
Relative air humidity	5 - 95 %
Protection class	IP40
Ambient temperature	-5 ... 50 °C
Max. tightening torque, wall mounting	6 Nm
Product weight	131.1 g
Electrical connection 1, connection technology	Cage clamp terminal
Cable outlet	Straight
Mounting method for sub-base	with through hole
Pneumatic connection, port 1	für Cartridge 15 mm
Pneumatic connection, port 5	für Cartridge 15 mm
Materials note	Conforms to RoHS
Material of connecting plate	PA-reinforced
Material cover	PA-reinforced
Material seals	NBR
Material sleeve	High alloy steel, non-corrosive
Material clip	High alloy steel, non-corrosive
Material nut	High alloy steel, non-corrosive