


Solenoid valve

MDH-5/2-3/4-D-4-24DC

Part number: 12457

FESTO

With pilot valve and manual override, no socket connector



Data sheet

Feature	Value
Valve function	5/2 monostable
Type of actuation	electrical
Width	76 mm
Standard nominal flow rate	6,000 l/min
Working pressure	3 ... 16 bar
Design structure	Piston slide
Type of reset	Air spring
Protection class	IP65
Nominal size	18 mm
Grid dimension	82 mm
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Conforms to standard	ISO 5599-1
Manual override	Pushing
ISO code	451
Type of piloting	Piloted
Pilot air supply	Internal
Flow direction	non reversible
Lap	Positive overlap
Switching time off	160 ms
Switching time on	120 ms
Duty cycle	100 %
Max. positive test pulse with logic 0	4,300 µs
Max. negative test pulse with logic 1	2,100 µs
Characteristic coil data	24 V DC: 6.8 W 48 V AC: 50/60 Hz, pick-up power 14.5 VA, holding power 9.9 VA
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-10 ... 60 °C
Sound pressure level	85 dB(A)
Ambient temperature	-10 ... 50 °C
Product weight	2,600 g
Electrical connection	Per DIN EN 175301-803
Mounting type	On subbase With through-hole and screw
Pilot exhaust port 84	M5
Pneumatic connection, port 1	Connection plate size 4 as per ISO 5599-1
Pneumatic connection, port 2	Connection plate size 4 as per ISO 5599-1
Pneumatic connection, port 3	Connection plate size 4 as per ISO 5599-1
Pneumatic connection, port 4	Connection plate size 4 as per ISO 5599-1
Pneumatic connection, port 5	Connection plate size 4 as per ISO 5599-1
Materials note	Conforms to RoHS
Material seals	NBR
Material housing	Aluminum