

Push-in sleeve QSH-12-10-20

Part number: 130721

FESTO

reducing.



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Nominal size | 7.1 mm |
| Assembly position | Any |
| Design | Straight design |
| Container size | 20 |
| Operating pressure for entire temperature range | -0.095 ... 0.6 MPa |
| Operating pressure complete temperature range | -0.95 ... 6 bar |
| Operating pressure for entire temperature range | -13.775 ... 87 psi |
| Temperature-dependent operating pressure | -0.095 ... 1.4 MPa |
| Temperature dependent working pressure | -0.95 ... 14 bar |
| Temperature-dependent operating pressure | -13.775 ... 203 psi |
| Maritime classification | see certificate |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:::] Water as per manufacturer's declaration at www.festo.com |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 ... 80 °C |
| Product weight | 2.2 g |
| Pneumatic connection, port 1 | Push-in sleeve diameter 12 mm |
| Pneumatic connection, port 2 | Push-in sleeve diameter 10 mm |
| color of release ring | blue |
| Materials note | Conforms to RoHS |
| Material housing | PBT |