


Sub-base kit DADP-SP-G9-20-R

Part number: 8173535

FESTO



Data sheet

Feature	Value
Size	20
Assembly position	Any
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-C1-L
RSBP classification to CD-0033	F1a
Cleanroom class	ISO class 6
Ambient temperature	-10 ... 60 °C
Max. stop force	300 N
Max. tightening torque	1.5 Nm
Tightening torque tolerance	± 15 %
Product weight	160 g
Mounting type	Direct mounting via threads
Materials note	Conforms to RoHS
Material stops	High alloy steel
Material seals	NBR
Material plate	Anodised wrought aluminium alloy
Material screws	Steel