


# compact cylinder ADN-32-35-I-PPS-A

Part number: 8179023

FESTO



## Data sheet

| Feature  | Value  |
|--|--|
| Stroke   | 35 mm  |
| Piston diameter  | 32 mm  |
| Piston rod thread  | M8   |
| Cushioning   | PPS: Self-adjusting pneumatic end-position cushioning                              |
| Assembly position  | Any  |
| Conforms to standard                                     | ISO 21287  |
| Piston-rod end   | Female thread  |
| Position detection                                       | For proximity sensor   |
| Variants   | Single-ended piston rod  |
| Operating pressure MPa                                   | 0.15 ... 1 MPa   |
| Operating pressure                                       | 1.5 ... 10 bar   |
| Mode of operation  | double-acting  |
| Operating medium   | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                           |
| Note on operating and pilot medium                       | Lubricated operation possible (subsequently required for further operation)        |
| Corrosion resistance classification CRC                  | 2 - Moderate corrosion stress  |
| PWIS conformity  | VDMA24364-B1/B2-L  |
| Cleanroom class  | ISO class 6  |
| Ambient temperature                                      | -20 ... 80 °C  |
| Impact energy in end positions                           | 1 J  |
| Cushioning length  | 4 mm   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 415 N  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance    | 483 N  |
| Moving mass with 0 mm stroke                             | 60 g   |
| Additional mass factor per 10 mm of stroke               | 9 g  |
| Basic weight for 0 mm stroke                             | 265 g  |
| Additional weight per 10 mm stroke                       | 30 g   |
| Mounting type  | with through hole<br>with internal (female) thread<br>with accessories<br>Optional |
| Pneumatic connection                                     | G1/8   |
| Materials note   | Conforms to RoHS   |
| Material of flange screw                                 | Steel  |
| Material cover   | Anodised wrought aluminium alloy   |
| Material seals   | TPE-U(PUR)   |
| Material piston rod                                      | High alloy steel   |
| Material cylinder barrel                                 | Smooth-anodised wrought aluminium alloy  |