



Parallel gripper DHPS-16-A

Part number: 1254043

★ Core product range

FESTO



Data sheet

Feature	Value
Size	16
Stroke per gripper jaw	5 mm
Max. replacement accuracy	≤ 0.2 mm
Max. angular gripper jaw backlash ax,ay	< 0.5 deg
Max. gripper jaw backlash Sz	< 0.02 mm
Rotationally symmetrical	≤ 0.2 mm
Repetition accuracy, gripper	< 0.02 mm
Number of gripper fingers	2
Assembly position	Any
Mode of operation	double-acting
Gripper function	Parallel
Design structure	Lever guided motion sequence
Guide	Plain-bearing guide
Position detection	For proximity sensor
Total gripping force at 0.6 MPa (6 bar, 87 psi), opening	210 N
Total gripping force at 0.6 MPa (6 bar, 87 psi), closing	190 N
Operating pressure MPa	0.2 ... 0.8 MPa
Working pressure	2 ... 8 bar
Operating pressure	29 ... 116 psi
Max. operating frequency of gripper	3 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	33 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	41 ms
Max. mass per external gripper finger	150 g
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F5
Ambient temperature	5 ... 60 °C
Gripping force per gripper jaw at 0.6 MPa (6 bar, 87 psi) opening	105 N
Gripping force per gripper jaw at 0.6 MPa (6 bar, 87 psi) closing	96 N
Mass moment of inertia	0.465 kgcm ²
Max. force on gripper jaw Fz static	150 N
Max. torque at gripper Mx static	8 Nm
Max. torque at gripper My static	8 Nm
Max. torque at gripper Mz static	8 Nm
Lubrication interval for guide components	10 Mio SP
Product weight	184 g
Mounting type	Internal thread and centering sleeve With through-hole and centering sleeve Optional
Pneumatic connection	M3
Materials note	Conforms to RoHS
Material cover cap	PA
Material housing	Hard anodised wrought aluminium alloy
Material gripper jaws	High alloy steel, non-corrosive