

# Servomotor EMMS-AS-70-MK-LS-RMB-S1

Part number: 1550949

FESTO

Without gear unit.



## Data sheet

Feature	Value
Ambient temperature	-10 ... 40 °C
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Insulation protection class	F
Rating class according to EN 60034-1	S1
Temperature monitoring	PTC resistor
Protection class	IP65
Shaft design Featherkey	DIN 6885 A 4 x 4 x 16
Electrical connector system	Plug
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Authorization	RCM Mark c UL us - Recognized (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU low voltage guideline
Nominal operating voltage DC	360 V
Nominal voltage DC	360 V
Type of winding switch	Star inside
Number of pole pairs	4
Standstill torque	2.56 Nm
Nominal torque	2.29 Nm
Peak torque	7.75 Nm
Nominal rotary speed	4,100 1/min
Max. speed	4,880 1/min
Nominal motor power	1,061 W
Nominal motor current	2.6 A
Peak current	10 A
Motor constant	0.864 Nm/A
Voltage constant, phase-to-phase	52.2 mVmin
Phase-phase winding resistance	6.71 Ohm
Phase-phase winding inductance	13.44 mH
Overall mass moment of inertia at power take-off	0.68 kgcm <sup>2</sup>
Product weight	2,900 g
Permissible axial shaft load	75 N
Permissible radial shaft load	200 N
Rotor position sensor	Absolute multi-turn encoder
Rotary position encoder interface	EnDat 22
Rotary position encoder measuring principle	Inductive
Rotor position encoder resolution	19 Bit
Brake holding torque	2 Nm
Operating voltage DC for brake	24 V
Power consumption, brake	11 W

Feature	Value
Mass moment of inertia of brake	0.07 kgcm <sup>2</sup>
Switching cycles, holding brake	10 million idle actuations (without friction work)
MTTF, subcomponent	76 years, rotary position encoder 1769 years, holding brake
MTTFd, subcomponent	152 years, rotary position encoder