

Compact cylinder


ADVU-100- -P-A-S2

Part number: 156019
Classic - do not use for new projects


FESTO

For proximity sensing. Piston-rod end with female thread
Modern alternatives can be found by entering the first four characters of the type code in the search field.

Type to be discontinued. Available until 2025. See Support Portal for alternative products.



Exemplary representation



Data sheet

Feature	Value
Stroke	1 ... 400 mm
Piston diameter	100 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Mode of operation	double-acting
Piston-rod end	Female thread
Design structure	Piston Piston rod
Position detection	For proximity sensor
Variants	Through piston rod
Operating pressure MPa	0.08 ... 1 MPa
Working pressure	0.8 ... 10 bar
Operating pressure	11.6 ... 145 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Impact energy in end positions	1 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	4,418 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	4,418 N
Mounting type	with through hole with accessories Optional
Pneumatic connection	G1/4
Material of flange screw	steel, galvanized
Material cover	Wrought Aluminum alloy
Material of dynamic seals	NBR TPE-U(PU)
Material piston rod	High alloy steel
Material cylinder barrel	Wrought Aluminum alloy