



# Compact cylinder

## ADVU-16- -A-P-A-S20

Part number: 156061  
Classic - do not use for new projects

FESTO

For proximity sensing. Piston-rod end with male thread  
Modern alternatives can be found by entering the first four characters of the type code in the search field.  
Type to be discontinued. Available until 2025. See Support Portal for alternative products.



### Data sheet

| Feature  | Value   |
|--|---|
| Stroke   | 1 ... 200 mm  |
| Piston diameter  | 16 mm   |
| Cushioning   | P: Flexible cushioning rings/plates at both ends                            |
| Assembly position  | Any   |
| Mode of operation  | double-acting   |
| Piston-rod end   | Male thread   |
| Design structure   | Piston<br>Piston rod  |
| Position detection                                       | For proximity sensor  |
| Variants   | Through, hollow piston rod  |
| Operating pressure MPa                                   | 0.13 ... 1 MPa  |
| Working pressure   | 1.3 ... 10 bar  |
| Operating pressure                                       | 18.85 ... 145 psi   |
| Operating medium   | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium                       | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC                  | 2 - Moderate corrosion stress   |
| PWIS conformity  | VDMA24364-B1/B2-L   |
| Ambient temperature                                      | -20 ... 80 °C   |
| Impact energy in end positions                           | 0.01 J  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 90 N  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance    | 90 N  |
| Mounting type  | with through hole<br>with accessories<br>Optional                           |
| Pneumatic connection                                     | M5  |
| Material of flange screw                                 | High alloy steel, non-corrosive   |
| Material cover   | Wrought Aluminum alloy  |
| Material of dynamic seals                                | NBR<br>TPE-U(PU)  |
| Material piston rod                                      | High alloy steel, non-corrosive   |
| Material cylinder barrel                                 | Wrought Aluminum alloy  |