


Servomotor EMMS-AS-40-S-LS-TM

Part number: 1578602

FESTO

Without gear unit.



Data sheet

Feature	Value
Ambient temperature	-10 ... 40 °C
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Insulation protection class	F
Rating class according to EN 60034-1	S1
Temperature monitoring	PTC resistor
Protection class	IP54
Electrical connector system	Plug
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Authorization	RCM Mark c UL us - Recognized (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU low voltage guideline
Nominal operating voltage DC	360 V
Nominal voltage DC	360 V
Type of winding switch	Star inside
Number of pole pairs	4
Standstill torque	0.16 Nm
Nominal torque	0.14 Nm
Peak torque	0.5 Nm
Nominal rotary speed	9,000 1/min
Max. speed	23,040 1/min
Nominal motor power	135 W
Nominal motor current	0.83 A
Peak current	3.3 A
Motor constant	0.172 Nm/A
Voltage constant, phase-to-phase	11 mVmin
Phase-phase winding resistance	20.5 Ohm
Phase-phase winding inductance	5.18 mH
Overall mass moment of inertia at power take-off	0.023 kgcm ²
Product weight	870 g
Permissible axial shaft load	12 N
Permissible radial shaft load	78 N
Rotor position sensor	Absolute multi-turn encoder
Rotary position encoder interface	EnDat 22
Rotary position encoder measuring principle	Inductive
Rotary position encoder resolution	19 Bit
MTTF, subcomponent	76 years, rotary position encoder
MTTFd, subcomponent	152 years, rotary position encoder