



# Standards-based cylinder CRDNGS-80- -PPV-A

Part number: 160894

FESTO

Corrosion resistant, as per ISO 15552, NF E 49 003.1 and UNI 10 290, for proximity sensing. With adjustable cushioning at both ends.



Exemplary representation

## Data sheet

Feature	Value
Stroke	10 ... 2,000 mm
Piston diameter	80 mm
Piston rod thread	M20x1,5
Based on the standard	ISO 15552
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Piston-rod end	Male thread
Design structure	Piston Piston rod Swivel clevis Tie rod Cylinder barrel
Position detection	For proximity sensor
Variants	End cap with swivelling rod eye
Operating pressure MPa	0.06 ... 1 MPa
Working pressure	0.6 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364-B2-L
Food-safe	See Supplementary material information
Ambient temperature	-20 ... 80 °C
Cushioning length	30 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	2,721 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	3,016 N
Moving mass with 0 mm stroke	1,018 g
Additional mass factor per 10 mm of stroke	39 g
Basic weight for 0 mm stroke	5,804 g
Additional weight per 10 mm stroke	92 g
Mounting type	with internal (female) thread with accessories Optional
Pneumatic connection	G3/8
Material cover	Stainless steel casting
Material seals	TPE-U(PU)
Material housing	High alloy steel, non-corrosive
Material piston	Wrought Aluminum alloy
Material piston rod	High alloy steel, non-corrosive
Material cylinder barrel	High alloy steel, non-corrosive
Material nut	High alloy steel, non-corrosive
Material bearing	POM
Collar nut material	High alloy steel, non-corrosive
Material tie rod	High alloy steel, non-corrosive