



Fiber-optic device SOEG-L-Q30-NA-K-2L

Part number: 165324
Product to be discontinued

FESTO

Type to be discontinued. Available until 2020. See Support Portal for alternative products.



Data sheet

Feature	Value
Conforms to standard	EN 60947-5-2
Authorization	RCM Mark c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Materials note	Free of copper and PTFE
Measurement method	Fiber-optic unit
Type of light	Red
Working range	0 ... 120 mm
Ambient temperature	-25 ... 55 °C
Switch output	NPN
Switching element function	Antivalent
Max. switching frequency	1,000 Hz
Max. output current	200 mA
Voltage drop	2 V
Short circuit strength	Pulsing
Operating voltage range DC	10 ... 30 V
Residual ripple	20 %
Idle current	25 mA
Polarity protected	for all electrical connections
Electrical connection	Cable 4-core
Cable length	2.5 m
Material cable sheath	TPE-U(PUR)
Size	30x30x15 mm
Mounting type	with through hole
Product weight	88 g
Material housing	PBT-reinforced
Operating status display	Yellow LED
Operating reserve display	Green LED
Setting options	Potentiometer
Upper limit of adjustment range	100 ... 400 mm
Setting range upper limit depends upon fiber-optics	100 mm for SOEZ-LLG-RT-0,5-M6 120 mm for SOEZ-LLK-RT-2,0-M6 280 mm for SOEZ-LLG-SE-0,5-M4 400 mm for SOEZ-LLK-SE-2,0-M4
Ambient temperature with flexible cable installation	-5 ... 55 °C
Protection class	IP65
Corrosion resistance classification CRC	2 - Moderate corrosion stress