



Proximity Sensor SIES-Q8B-NS-K-L

Part number: 178292

FESTO

Inductive, with cable, can be flush-mounted, normally-open function, negative-switching.



Data sheet

Feature	Value
Conforms to standard	EN 60947-5-2
Authorization	RCM Mark c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Materials note	Conforms to RoHS
Nominal switching distance	1.5 mm
Guaranteed switching distance	1.2 mm
Reduction factors	Aluminum = 0.45 Stainless steel, St 18/8 = 0.8 Copper = 0.4 Brass = 0.55 Steel, St 37 = 1.0
Ambient temperature	-25 ... 70 °C
Repetition accuracy	0.07 mm
Switch output	NPN
Switching element function	Normally open contact
Max. switching frequency	3,500 Hz
Max. switching frequency, DC	1,500 Hz
Max. output current	200 mA
Voltage drop	2 V
Short circuit strength	Pulsing
Operating voltage range DC	10 ... 30 V
Residual ripple	10 %
Idle current	≤ 10 mA
Polarity protected	for all electrical connections
Electrical connection	3-core Cable
Cable length	2.5 m
Material cable sheath	TPE-U(PUR)
Size	8x8x40 mm
Mounting type	with internal (female) thread
Type of installation	flush
Product weight	39 g
Material housing	Zinc die-casting Chromed-plated Nickel plated
Operating status display	Yellow LED
Protection class	IP67
PWIS conformity	VDMA24364-B2-L