


Motor cable

NEBM-M40G8-E-10-Q10N-LE8

Part number: 1750242
Product to be discontinued

For EMMS-AS-190 with CMMP-AS.

FESTO



Data sheet

Feature	Value
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Plug socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M40x1,5
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Operating voltage range DC	0 ... 630 V
Note on operating voltage range DC	0 - 300 V for 0.75 mm ²
Operating voltage range AC	0 ... 630 V
Note on operating voltage range AC	0 - 300 V for 0.75 mm ²
Acceptable current load at 40°C	22 A
Note on acceptable current load at 40°C	12 A for 0.75 mm ²
Surge strength	4 kV
Note on surge resistance	2.5 kV for 0.75 mm ²
Cable length	10 m
Cable attribute	Suitable for chain link trunking
Bending radius, fixed cable installation	≥ 70 mm
Bending radius, flexible cable installation	≥ 140 mm
Cable diameter	14 mm
Cable structure	4x2,5+2x(2x0,75) Shielded
Nominal conductor cross-section	0.75 mm ² 2.5 mm ²
Wire ends	Wire end ferrule
Protection class	IP65
Note on degree of protection	in assembled condition
Ambient temperature	-50 ... 90 °C
Ambient temperature with flexible cable installation	-40 ... 90 °C
CE symbol (see declaration of conformity)	according to EU low voltage guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materials note	Conforms to RoHS
Degree of contamination	3
Corrosion resistance classification CRC	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath color	Orange
Material insulation	TPE-E