


Short stroke cylinder

AEVC-12-5-A-P-A

Part number: 188084
Product to be discontinued

FESTO

For proximity sensing, piston-rod end with male thread.
Type to be discontinued. Available until 2026. See Support Portal for alternative products.



Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	12 mm
Spring return force, retracted	4 N
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Mode of operation	single-acting pushing action
Design structure	Piston Piston rod
Position detection	For proximity sensor
Operating pressure MPa	0.15 ... 1 MPa
Working pressure	1.5 ... 10 bar
Operating pressure	21.75 ... 145 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	59 N
Moving mass	8.4 g
Product weight	58 g
Mounting type	with through hole with accessories Optional
Pneumatic connection	M5
Materials note	Conforms to RoHS
Material cover	Wrought Aluminum alloy Anodized
Material seals	TPE-U(PU)
Material housing	Wrought Aluminum alloy Anodized
Material piston rod	High alloy steel