

# Standards-based cylinder DSNU-25-60-PPS-A

Part number: 1908325

FESTO

with self-adjusting pneumatic end position cushioning



## Data sheet

| Feature  | Value   |
|--|---|
| Stroke   | 60 mm   |
| Piston diameter  | 25 mm   |
| Piston rod thread  | M10x1,25  |
| Cushioning   | PPS: Self-adjusting pneumatic end-position cushioning                       |
| Assembly position  | Any   |
| Conforms to standard                                     | CETOP RP 52 P<br>ISO 6432   |
| Piston-rod end   | Male thread   |
| Design structure   | Piston<br>Piston rod<br>Cylinder barrel                                     |
| Variants   | Single-ended piston rod   |
| Operating pressure MPa                                   | 0.1 ... 1 MPa   |
| Working pressure   | 1 ... 10 bar  |
| Mode of operation  | double-acting   |
| Operating medium   | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium                       | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC                  | 2 - Moderate corrosion stress   |
| PWIS conformity  | VDMA24364-B1/B2-L   |
| Cleanroom class  | ISO class 6   |
| Ambient temperature                                      | -20 ... 80 °C   |
| Impact energy in end positions                           | 0.3 J   |
| Cushioning length  | 17 mm   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 247.4 N   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance    | 294.5 N   |
| Moving mass with 0 mm stroke                             | 71 g  |
| Additional mass factor per 10 mm of stroke               | 6 g   |
| Basic weight for 0 mm stroke                             | 238 g   |
| Additional weight per 10 mm stroke                       | 11 g  |
| Mounting type  | with accessories  |
| Pneumatic connection                                     | G1/8  |
| Materials note   | Conforms to RoHS  |
| Material cover   | Wrought Aluminum alloy<br>neutral anodization                               |
| Material seals   | NBR<br>TPE-U(PU)  |
| Material piston rod                                      | High alloy steel, non-corrosive   |
| Material cylinder barrel                                 | High alloy steel, non-corrosive   |