



Compressed air reservoir VZS-20-B

Part number: 192161

FESTO



Data sheet

Feature	Value
Volume	20 l
Assembly position	Downward condensate drain
Conforms to standard	EN 286-1
Operating pressure MPa	-0.095 ... 1.6 MPa
Working pressure	-0.95 ... 16 bar
Operating pressure	-13.775 ... 232 psi
CE symbol (see declaration of conformity)	According to EU simplified Pressure Vessel Directive
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-::-] Nitrogen
Corrosion resistance classification CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-10 ... 100 °C
Ambient temperature	-10 ... 100 °C
Max. tightening torque, connecting thread	130 Nm
Max. tightening torque, condensate drain	27 Nm
Product weight	9,000 g
Mounting type	with through hole
Condensate drain connection	G3/8
Pneumatic connection	G1
Material of air reservoir	steel, powder-coated