

Lubricator



LOE-1/2-D-MAXI

Part number: 186480
Classic - do not use for new projects

FESTO

With metal bowl guard.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

Feature	Value
Size	Maxi
Series	D
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Max. oil capacity	190 cm ³
Bowl guard	Metal bowl guard
Working pressure	0 ... 16 bar
Minimum flow rate for lubricator function	10 l/min
Standard nominal flow rate	8,300 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:4:-] Inert gases
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	1,100 g
Mounting type	with accessories
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Materials note	Conforms to RoHS
Material bowl	PC