

Standard cylinder



CDN-40- -PPV

Part number: 193661

FESTO

In accordance with ISO 15552, with increased corrosion resistance and easy-to-clean design.

Depending on the configuration, the illustrations, the technical data on the data sheet and the relevant accessories might not exactly match this product.



Exemplary representation

Data sheet

~ConfIndependentDatasheet

Feature	Value
Stroke	10 ... 2,000 mm
Piston diameter	40 mm
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Conforms to standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Design structure	Piston Piston rod
Position detection	For proximity sensor
Variants	For unlubricated operation Extended male piston rod thread Female thread on piston rod Extended piston rod Through piston rod Heat resistant seals, max. 120°C Single-ended piston rod
Working pressure	0.6 ... 12 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Corrosion resistance classification CRC	3
Ambient temperature	-20 ... 120 °C
Cushioning length	20 mm
Theoretical force at 6 bar, return stroke	633 N
Theoretical force at 6 bar, advance stroke	754 N
Mounting type	with internal (female) thread with accessories Optional
Pneumatic connection	G1/4
Materials information for cover	Wrought Aluminum alloy Anodized
Materials information for piston rod	High alloy steel, non-corrosive
Materials information for cylinder barrel	Wrought Aluminum alloy Anodized