

# Short stroke cylinder

## AEVC-20-5-I-P

Part number: 188131  
Product to be discontinued

FESTO

No facility for sensing, piston-rod end with female thread.  
Type to be discontinued. Available until 2026. See Support Portal for alternative products.



### Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	20 mm
Spring return force, retracted	5 N
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Mode of operation	single-acting pushing action
Design structure	Piston Piston rod
Position detection	No
Operating pressure MPa	0.15 ... 1 MPa
Working pressure	1.5 ... 10 bar
Operating pressure	21.75 ... 145 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	180 N
Moving mass	14 g
Product weight	52 g
Mounting type	with through hole with accessories Optional
Pneumatic connection	M5
Materials note	Conforms to RoHS
Material cover	Wrought Aluminum alloy Anodized
Material seals	NBR TPE-U(PU)
Material housing	Wrought Aluminum alloy Anodized
Material piston rod	High alloy steel