


# Round cylinder CRHD-32- -PPV-A-MS-S6

Part number: 195555

FESTO

Corrosion-resistant, smooth bearing cap, end cap with drawbolt catch , heat-resistant design to 120 °C

The S6 variant (heat resistant) is not intended for direct contact with food products due to the utilized seals and grease.



Exemplary representation



## Data sheet

| Feature  | Value   |
|--|---|
| Stroke   | 10 ... 500 mm   |
| Piston diameter  | 32 mm   |
| Cushioning   | PPV: Pneumatic cushioning adjustable at both ends                           |
| Assembly position  | Any   |
| Design structure   | Piston<br>Piston rod  |
| Position detection                                       | For proximity sensor  |
| Variants   | Heat resistant seals, max. 120°C  |
| Working pressure   | 1 ... 10 bar  |
| Mode of operation  | double-acting   |
| Operating medium   | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium                       | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC                  | 3 - High corrosion stress   |
| PWIS conformity  | VDMA24364-B2-L  |
| Food-safe  | See Supplementary material information                                      |
| Ambient temperature                                      | -20 ... 120 °C  |
| Cushioning length  | 17 mm   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 415 N   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance    | 483 N   |
| Moving mass with 0 mm stroke                             | 106 g   |
| Additional mass factor per 10 mm of stroke               | 9 g   |
| Basic weight for 0 mm stroke                             | 640 g   |
| Additional weight per 10 mm stroke                       | 26 g  |
| Pneumatic connection                                     | G1/8  |
| Material cover   | High alloy steel, non-corrosive   |
| Material seals   | FPM   |
| Material housing   | High alloy steel, non-corrosive   |
| Material piston rod                                      | High alloy steel, non-corrosive   |