



# Short stroke cylinder AEVC-100-25-I-P-A

Part number: 188325  
Product to be discontinued

FESTO

For proximity sensing, piston-rod end with female thread.  
Type to be discontinued. Available until 2026. See Support Portal for alternative products.



## Data sheet

| Feature   | Value   |
|---|---|
| Stroke  | 25 mm   |
| Piston diameter                                       | 100 mm  |
| Spring return force, retracted                        | 140 N   |
| Based on the standard                                 | ISO 6431<br>Hole pattern<br>VDMA 24562                                      |
| Cushioning  | P: Flexible cushioning rings/plates at both ends                            |
| Assembly position                                     | Any   |
| Mode of operation                                     | single-acting<br>pushing action   |
| Design structure                                      | Piston<br>Piston rod  |
| Position detection                                    | For proximity sensor  |
| Operating pressure MPa                                | 0.1 ... 1 MPa   |
| Working pressure                                      | 1 ... 10 bar  |
| Operating pressure                                    | 14.5 ... 145 psi  |
| Operating medium                                      | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium                    | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC               | 1 - Low corrosion stress  |
| PWIS conformity                                       | VDMA24364-B1/B2-L   |
| Ambient temperature                                   | -20 ... 80 °C   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 4,503 N   |
| Moving mass   | 604 g   |
| Product weight  | 2,250 g   |
| Mounting type   | with through hole<br>with accessories<br>Optional                           |
| Pneumatic connection                                  | G1/4  |
| Materials note  | Conforms to RoHS  |
| Material cover  | Wrought Aluminum alloy<br>Anodized  |
| Material seals  | TPE-U(PU)   |
| Material housing                                      | Wrought Aluminum alloy<br>Anodized  |
| Material piston rod                                   | High alloy steel  |