


Parallel kit EAMM-U-50-D32-40P-78

Part number: 2153283

★ Core product range

Suitable for electric drives.

FESTO



Data sheet

Feature	Value
Size	50
Assembly position	Any
Gear unit ratio	1:1
Max. speed	6,000 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	12.1 kgmm ²
No-load driving torque	0.01 Nm
Transferable torque	1 Nm
Product weight	596 g
Interface code, actuator	D32B
Interface code, motor in	40P
Materials note	Conforms to RoHS